

# **TECHNICAL DATA SHEET**

Prusament PLA by Prusa Polymers



PLA is the most commonly used filament. It's biodegradable, easy to print, and very strong. The perfect choice for printing large objects thanks to its low thermal expansion (little to no warping) and for printing tiny parts because of its low melting temperature.

#### **APPLICATIONS:**

Concept models, functional prototypes, low-wear toys, etc.

# **NOT SUITABLE FOR:**

Long term outdoor usage because of low temperature resistance (up to 60 °C).

#### **POST-PROCESSING:**

Wet sanding. Without water you'll quickly start heating the plastic by friction, it will melt locally and make it hard to keep sanding.

## **IDENTIFICATION:**

Trade name	Prusament PLA		
Chemical name	Polylactic Acid		
Usage	FDM 3D printing		
Manufacturer	Prusa Polymers, Prague, Czech Republic		

## **RECOMMENDED PRINT SETTINGS:**

Nozzle Temperature [°C]	210 ± 10
Heatbed Temperature [°C]	40-60
Print Speed [mm/s]	up to 200



## TYPICAL MATERIAL PROPERTIES:

Physical Properties	Typical Value	Method	
Peak Melt Temperature [°C]	145-160	ISO 11357	
Glass Transition Temperature [°C]	55-60	ISO 11357	
MFR [g/10min] <sup>(1)</sup>	10.4=	ISO 1133	
MVR [cm³/10min] <sup>(1)</sup>	9.4	ISO 1133	
Specific Gravity [g/cm³]	1.24	ISO 1183	
Moisture Absorption 24 hours [%](2)	0.3	Prusa Polymers	
Moisture Absorption 7 days [%](2)	0.3	Prusa Polymers	
Moisture Absorption 4 weeks [%](2)	0.3	Prusa Polymers	
Heat Deflection Temperature (0,45 MPa) [°C]	55	ISO 75	
Tensile Yield Strength Filament [MPa]	57.4 ± 0.4	ISO 527-1	

 $<sup>^{(1)}</sup>$  2,16 kg; 210 °C |  $^{(2)}$  28 °C; humidity 37 %

# **MECHANICAL PROPERTIES OF PRINTED TESTING SPECIMENS**(3):

Property / print direction	Horizontal	Vertical X,Y-Axis	Vertical Z-Axis	Method
Tensile Modulus [GPa]	2,2 ± 0,1	2,4 ± 0,1	2,3 ± 0,1	ISO 527-1
Tensile Yield Strength [MPa]	50,8 ± 2,4	59,3 ± 1,9	37,6 ± 4,0	ISO 527-1
Elongation at Yield Point [%]	2,9 ± 0,3	3,2 ± 0,1	1,9 ± 0,3	ISO 527-1
Impact Strength Charpy <sup>(4)</sup> [kJ/m <sup>2</sup> ]	12,7 ± 0,7	13,7 ± 0,7	5,0 ± 1,4	ISO 179-1

<sup>(3)</sup> Original Prusa i3 MK3 3D printer was used to print testing specimens. Slic3r Prusa Edition 1.40.0 was used to create G-codes with following settings: Prusa PLA Filament; Print settings 0,20mm FAST (layers 0,2mm); solid layers Top: 0 Bottom: 0; Infill 100% Rectilinear, infill print speed 200mm/s; extruder temperature 215°C all layers; bed temperature 60°C all layers; other parameters set to default | (4) Charpy Unnotched, edgewise direction of blow according to ISO 179-1

#### **DISCLAIMER**

The results presented in this data sheet are just for your information and comparison. Values are significantly dependent on print settings, operators experiences and surrounding conditions. Everyone have to consider suitability and possible consequences of printed parts usage. Prusa Polymers can not carry any responsibility for injures or any loss caused by using of Prusa Polymers material.

